

Micrograph laboratory Microlab ML3700

Tabletop laboratory for making cross-section analysis



With the Microlab you can prepare microsections of crimped contacts in a very professional and comfortable manner.

The Microlab product family is designed to prepare cross sections of conductor crimps and insulation crimps easily and comfortably within a few minutes. After cutting, polishing and etching of the sample, the image of the cross section can be visualized on the screen. Now a comprehensive quality check of the crimp can be performed by using the special designed image processing software X-Scan.

Equipped with a high quality 12x zoom objective the **Microlab ML3700** is the ideal tool to conduct quality tests quick and comfortable. The high resolution camera delivers first-class microsections which can be easily measured with the automatic function of the image processing software **X-Scan**. Automatically generated records can be used as proofs of quality. Of course, X-Scan fulfills all relevant DIN standards and OEM specifications.

Performance features

- Complete micrograph laboratory integrated in a MDF board
- Easily operated optic with 12x zoom objective with an outstanding combination of zoom and resolution
- First-class Digital color camera USB 2.0 with special photosensitive CMOS Sensor and 1.3 megapixel resolution
- Well suited for cross sections from **0.1 to 10 mm**² (AWG 28 AWG 10)
- Comfortable analysis software X-Scan



C-tec Cable technologies GmbH & Co.KG

Ilztalstraße 11 Tel.: +49 (0) 8554 – 94 23 9-0 D-94513 Schönberg Fax: +49 (0) 8554 – 94 23 9-20













Cutting the crimp



Optic with camera



Finished microsection with X-Scan

Performance features in detail

- © Complete system, integrated ergonomically and functionally in a MDF board laminated with stainless steel
- High quality optic with 12x zoom objective and **convenient focusing** (coarse and fine adjustment)
- High performance Digital color camera with photosensitive 1.3 Megapixel CMOS-Sensor, optical class 1/1.8", USB 2.0, 1280x1024 Pixel
- Suitable for small and medium contact sizes from 0.1 to 10 mm²
- Standard terminal holder for cross sections up to 6 mm² (further sizes available on request)
- Longlife LED illumination at the microscope
- Energy saving working lamp for the Cutting-/Grinding unit
- Fitting gas tight mount for 7 calibration gauges
- Appropriate tool set for the sample preparation
- With comfortable analysis software X-Scan
- Compact dimensions
- Software calibration based on traceable standards incl. calibration certificate
- Cross-sectioning of the sample can be carried out without any disturbance of the terminal and cable stranding
- Optional: ancillary lens 0.5x for 12x zoom objective for extended applications

Specifications

Type

Voltage supply

Smallest extension (15" monitor)

Largest extension (15" monitor)

Smallest crimp height for a full screen

Largest crimp height for a full screen

6 Measurement resolution µm per pixel

6 Optical zoom grades

Camera resolution

Camera connection

6 Object illumination

Fine polishing

Cross section sizes standard

Recommended temperature

Dimensions (W x D x H)

Weight

ML 3700/EFP

100 - 240 VAC 50/60 Hz

24x

288x

0.25 mm

8.0 mm

13 -7.31- 5.17-3.72-3.00-2.45- 2.10- 1.84-1.64-1.47- 1.34- 1.23- 1.14- 1.06-

0.58 - 1.0 - 1.5 - 2.0 - 2.5 - 3.0 - 3.5 - 4.0 - 4.5 - 5.0 - 5.5 - 6.0 - 6.5 - 7.0

1280 x 1024 Pixel

USB 2.0 Port (Type: mini USB plug)

Longlife LED ring light for true to color pictures

Electrochemical

0.1mm² - 10mm² (AWG 28 - AWG 10)

22°C +/- 5°

1200mm x 430mm x 500mm

27 kg



Quality Management

ISO 9001

C-tec Cable technologies GmbH & Co.KG

Ilztalstraße 11 D-94513 Schönberg Tel.: +49 (0) 8554 - 94 23 9-0

Fax: +49 (0) 8554 - 94 23 9-20

eMail: info@cable-tec.net DEKRA HP: www.cable-tec.net

Environmental Management ISO 14001